

INSTALLATION INSTRUCTIONS FOR 281 SERIES CLOSURE AND PARALLEL ARMS APPLICATION

PH4 Arm

FOR INSTALLATION ASSISTANCE, CALL SARGENT AT 1-800-727-5477 • www.sargentlock.com

IMPORTANT: USE ALTERNATE MOUNTING IF DOOR CAN OPEN BEYOND LIMITS SHOWN FOR STANDARD MOUNTING							
ARM TYPE	DESCRIPTION	STANDARD MOUNTING			ALTERNATE MOUNTING		
		DIM.		MAX. DOOR OPENING	DIM.		MAX. DOOR OPENING
PH4	90°-180° HOLDER ARM	4 1/2*	10 1/2*	110°	1 5/8*	7 5/8°	180°





- A DOOR CLOSER BODY INTERFERES WITH A DOOR LIGHT KIT, USE 281-B MOUNTING PLATE. PLATE TO BE MOUNTED INVERTED, SEE DATA SHEET A7242 FOR DETAILS.
- SPACE REQUIRED TO MOUNT CLOSER ON RAIL. IF SPACE IS LESS THAN SHOWN USE 281-D DROP PLATE.
 SEE DATA SHEET A7244 FOR DETAILS.
- 3-THIS DIMENSION IS TAKEN FROM HINGE DOOR FOR INVISIBLE HINGES.
- 2-L LEFT HAND DOOR SHOWN. RIGHT HAND DOOR OPPOSITE.

HEAD

1-12 GAUGE MIN. REINFORCEMENT REQUIRED FOR METAL DOORS & FRAMES.

SARGENT

ASSA ABLOY

ASSA ABLOY, the global leader in door opening solutions