



Cover Pan No.	Pan Depth	Spindle Size	Door Mortise
3910-1	7/8 (22)	1/2" Longer	13/16 (20.6)
3910-2	1/4 (6.4)	Regular	11/16 (17.5)
3910-3	3/8 (9.5)	Regular	9/16 (14.3)
3910-4	1/2 (12.7)	Regular	1/2 (12.7)
3910-5	5/8 (15.9)	1/2" Longer	11/16 (17.5)
3910-6	3/4 (19)	1/2" Longer	15/16 (23.8)
3910-7	1 (25.4)	1/2" Longer	11/16 (17.5)
3910-8	1-1/4 (31.8)	1" Longer	11/16 (17.5)
3910-9	1-1/2 (38.1)	1" Longer	1/2 (12.7)
3910-10	1-3/4 (44.4)	1-1/2" Longer	5/8 (15.9)
3910-11	2 (50.8)	1-1/2" Longer	9/16 (14.3)

Notes:

1. Do not scale drawing.
2. This template can be used with standard 3/4" (19) offset arm.
3. For additional installation details see template OS10080.
4. Set cement case 1/8" (3.2) lower than depth of cover pan ordered. Use cover pan to facilitate installation of cement case.
5. Brass alignment pins furnished to align pan with closer. Pan is not fastened to floor closer.
6. Provide 1/16" (1.6) clearance around cover pan.
7. All dimensions are given in inches (mm).

CAUTION: Prevent grout from collecting between the closer and cement case in the event closer must be removed after the grout is set.

Cover Pan for L27 Closer All Depths

RIXSON

ASSA ABLOY

www.rixson.com

TEMPLATE NUMBER

MS140050

DATE

03-16