



Product Release Information: AD-Series Firmware AD.A.133

Product	AD-Series
Version Number	Firmware Package: AD.A.133
Firmware Release Date	November 2020
Customer Support	For more information or support, visit our document library .

Attention:

This document contains the **Release Notes** for AD-Series Firmware Package AD.A.133. This update includes updates and improvements made after the AD.A.132 firmware package released in July 2020.

Installation and Update Notes:

Installation

Refer to the “Device Firmware Update” Section of the SUS User Guide – Appendix B for full details. You can find the latest SUS User Guide [here](#) with additional Quick Start information at the Support Library [here](#) by searching for “SUS Quick Start”.

Who should update?

Allegion recommends keeping all devices up to date with the latest firmware and software. We strive to provide the best products and service for our customers.

Our latest firmware and software releases will allow the customer to get the most from their devices.

Specifically, all customers who would be interested in the following New Feature and Recent Changes should update:



New Features:

- **MTK2 Reader Family:**
 - Implemented features needed for Allegion Mifare2Go
 - Requires a configuration card to enable
 - This feature is intended for use under PACS management

NOTE: When Using Allegion Mifare2Go or other Mobile Credential types, SUS should not be used to modify Reader “Card Technology” settings.

Recent Changes:

- **MTK2 Reader Family:**
 - Implemented fix for Card+PIN credentials failing to grant access when Apple Student ID or Transact NFC are enabled on the reader
 - Improved read response for Prox cards

Version Compatibility:

The AD.A.133 Package contains the following individual product firmware versions:

NOTE: All Devices that have been updated in the AD.A.133 release are listed in **bold** in the table below:

Devices	Firmware Version
AD-200	2.51.0
AD-250	2.50.0
AD-300	2.51.0
AD-302	2.3.0
AD-400	2.51.0
AD-402	2.3.0
KP-PR-SM-MT	2.48.0
KP-PR-SM-MT2	2.7.1
MG	2.44.0
PIB300-2D	2.19.1
PIM400-485-RSI	2.30.1
PIM400-485-VBB	2.30.1
PIM400-TD2	2.26.0
WPR400	2.31.0
WRI400	2.9.2
CT5000	2.8.0